

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS



FED. MFR. CODE 91929

ACTUATOR - SWITCH

CATALOG LISTING

JS-45

(M) JS-45
ISSUE 2

REPLACES

CATALOG LISTING

JS-45

PAGE 1 OF 1

M

ISSUE

10

RELEASE NO.

11 MAY 56

C.N.T.

CHECK

10 MAY 56

B.L.S.

CHECK

17 MAY 56

G.C.H.


CHECK

2 MAY 56

R.E.R.

REVISIONS

A	CO 10437	R.E.R.	58
B	CO 12901	M.B.F.	13 MAY 59
C	CO 31462	R.E.R.	18 DEC 72
D	CO 47771	C.J.H.	17 MAY 80
E	CO 62122	T.S.K.	22 AUG 87
F	CO 66329	T.S.M.	15 MAR 91
G	CO 79303	D.L.T.	7 MAR 95
H	0000470	C.S.L.	5 JUN 03



NOTE $\triangle$ FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH ISM BASIC SWITCH INSTALLED

OPERATING FORCE ----- 7 OZ. MAX.

RELEASE FORCE ----- 2 OZ. MIN.

PRETRAVEL ----- .219 MAX.

DIFFERENTIAL TRAVEL ----- .020 MAX.

OVERTRAVEL ----- .030 MIN.

ELECTRICAL DATA

CONTACT ARRANGEMENT

BREAK DISTANCE

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	$\pm$.030
TWO PLACE	(.00)	$\pm$.015
THREE PLACE	(.000)	$\pm$.005
ANGLES		$\pm$

WEIGHT

RASTER

DRAWN

74-96