



**Part Number :** [936010040](#)  
**Product Description :** GWconnect Turned Crimp Contact for 10A Inserts and Modules, Female, Gold (Au) Plated Copper Alloy, 0.14-0.37mm<sup>2</sup> (26-22 AWG), 100 per Bag  
**Series Number :** 93601  
**Status :** Active  
**Product Category :** Heavy-Duty Contacts  
**Engineering Number :** 7100.4201.1



## Documents & Resources

**Drawings**  
[936010040\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Heavy-Duty Contacts
Series	93601
Description	GWconnect Turned Crimp Contact for 10A Inserts and Modules, Female, Gold (Au) Plated Copper Alloy, 0.14-0.37mm <sup>2</sup> (26-22 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Name	GWconnect
UPC	887191866185

### Agency

CSA	256883
UL	E249674

### Electrical

Current - Maximum per Contact	10.0A
-------------------------------	-------

### Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Gold
Net Weight	0.700/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	8.00mm
Wire Size (AWG)	22, 24, 26
Wire Size mm <sup>2</sup>	0.14-0.37

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>

### Use with Part(s)

Description	Part Number
Use With	S-D, S-DD, S-K, S-Q, S-QD, and S-M Inserts

---

This document was generated on Feb 06, 2025