



Representative Image

Catalog No. RB873

Description: INSNYL RING TRM 18-14 BLT NO10 BLUE

UPC No 786210818795

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Nylon Insulated Ring Terminal, Length .89 Inches, Width .31 Inches, Maximum Insulation .162, Bolt Hole #10, Wire Range #18-#14 AWG, Color Blue, Copper, Tin Plated, 1,000 Pack

Descriptors

Category	Electrical terminals
Special Features	Self-insulated with high dielectric-strength nylon sleeves. An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep.

Specifications

Voltage Rating	600 V
Material	Copper
Color	Blue

Classifications

Brand Name	Sta-Kon
Standard	UL E9809

Dimensions

Wire Size	18-14 AWG
-----------	-----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Blue
Reel packaging	N
AWG-range	18-14

by ABB

ETIM	EC001052 Solderless copper terminals for copper conductors
Material	Copper
Surface protection	Tinned
Stud size (imperial)	10

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A