


THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USE.

DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAT, HERDRUKT, OVERGEMAAT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFFELIJKE TOELATING. BIJ NIET GEBRUIK IS TERUGZENDING VERPLICHT.



PERFORMANCE CHARACTERISTICS

CURRENT RATING : 1.5 A AT 20°C (FULLY LOADED)
RATED VOLTAGE : 500 V AC (CONT / CONT)
OPERATING TEMPERATURE : -55°C TO 125°C
CONTACT RESISTANCE : 20 mΩ MAX
INSERTION FORCE : 0.75 N MAX / CONT
EXTRACTION FORCE : 0.15 N MIN / CONT
INSULATION RESISTANCE : 10^4 MΩ MIN

CAT. NR.	L *0.3	DESCRIPTION
HM2P08PD5110----	3.7	SHORT PRESS-FIT
HM2P08PC5110----	4.5	SHORT PRESS-FIT
HM2P08PK5110----	13	REAR PLUG-UP: LEVEL 1
HM2P08PM5110----	14.5	REAR PLUG-UP: LEVEL 2
HM2P08PN5110----	16	REAR PLUG-UP: LEVEL 3
HM2P08PT5110----	13	WIRE WRAP

NOTES

PERFORMANCE LEVEL INDICATOR

(BEEFR DWG No BS C 201844 003)

1. "HM2P08P#5110" REFER Dwg No. DYC-1201044-005
LEAD FREE INDICATOR : LF=LEAD FREE
(RIGHT 15816)

2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
3. MEASURED AT THE BOTTOM.
4. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING : BSA ,201572,001
5. THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008

MALE SIGNAL STRAIGHT PRESS-FIT-TO-BOARD CONNECTOR
WITHOUT SERVICECENTER (WIDE BODY)

WITHOUT SERVICE CENTER (WIDE BODY)				
1DEC ± 0,2 2DEC ± 0,1 ANGLES ± 1°	APPR.	DATE	SIGN.	MILLIPACS 2 / TYPE B / NO SHIELDING
	DRAFT	1993-06-08	W. Panis	CAT. No. HM2P08P#5110-----
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	PROD. MGR.			SCALE
	PR. ENG. MGR.			
ALL DIMENSIONS IN MM	PR. MGT. MGR.			3 / 1



REFERENCES

BS, C, 201632, 002

AWING No. _____ CUSTOMER DRAWING _____ REVISION _____

PDM: Rev:C STATUS: Released Printed: Mar 27, 2010