

M474A1K43DB1-CTD



Error correction code UDIMM / SODIMM

Single error correction and detection available
Supports x8 up to 2 ranks per DIMM
Application : High-end desktop, High-end laptop, Ser

Cookies

This site uses cookies to personalise your experience, analyse site traffic. By Clicking Accept or continuing to browse the site you are agreeing to our use of cookies.
You can read our [Privacy Policy](#) and [Cookie Policy](#) for more information.

Accept

Specification



DDR
DDR4



Dimm Type
ECC SODIMM



Density
8 GB



Rank x Organization
1R x 8



Speed
2666 Mbps



Voltage
1.2 V



Number of Pins
260



Component Composition
(1G x 8) x 9



Product Status
Mass Production

Related Resources



Samsung DRAM Module Handling Guide
Handling guide

Download

Related Contents



Sorry, no matches were found.

* All product specifications reflect internal test results and are subject to variations by the user's system configuration.
* All product images shown are for illustration purposes only and may not be an exact representation of the product.
* Samsung reserves the right to change product images and specifications at any time without notice.