



Color: ☐ multi-colored

Physical data		
Pin spacing		3 mm
Blade width		2.5 mm
Blade length		40 mm
Handle length		100 mm
Mechanical data		
Suitable		for 2059 Series
Drive type		Operating
Continuous blade		No
Blade design		gerade
Anti-roll protection		Yes
Hanging loop		Yes
Handle marking		Yes
Material data		
Color		multi-colored
Material 1		Polypropylen (PP)
Material 2		Thermoplastische Elastomere (TPE)
Fire load		0 MJ
Blade surface		brüniert
Weight		24.5 g
Commercial data		
Product Group		14 (Tools)
PU (SPU)		5 (1) pcs
Packaging type		Box
Country of origin		DE
GTIN		4050821836407
Customs tariff number		82055980000



Product classification		
UNSPSC		27111601
eCl@ss 10.0		27-14-11-92
eCl@ss 9.0		27-14-11-92
ETIM 9.0		EC002848
ETIM 8.0		EC002848
ECCN		NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads


Environmental Product Compliance

Compliance Search

Environmental Product Compliance 206-859

↓

Installation Notes



Insert/remove solid conductors by lightly pressing on push-button.