Part Number : 1722564108
Product Description : Ultra-Fit Tangless Receptacle Housing, 3.50mm Pitch, Single Row, 8 Circuits, Natural, Glow-Wire Capable
Series Number : 172256
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

1722564108_sd.pdf

1723230004-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

1723230003-000.pdf

1723230001-TS-000.pdf

1723231000-PS-CH-000.pdf

1723231000-PS-ES-000.pdf

1723231000-PS-JP-000.pdf

1723231000-PS-SK-000.pdf

PS-172323-0001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC

Downloaded from Arrow.com.

	61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	172256
Description	Ultra-Fit Tangless Receptacle Housing, 3.50mm Pitch, Single Row, 8 Circuits, Natural, Glow-Wire Capable
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Ultra-Fit
UPC	191130133932

Agency

CSA	LR19980
UL	E29179

Downloaded from Arrow.com.

Physical

Circuits (maximum)	8
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	2.571/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C, -40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 8 Circuits, with Kinked Pins, Tin (Sn) Plating, Natural, Glow-Wire Capable	1722862108
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 8 Circuits, with Kinked Pins, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable	1722862208
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 8 Circuits, with Kinked Pins, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable	1722862308
Ultra-Fit Vertical Header, 3.50mm	1722872108

Downloaded from Arrow.com.

Pitch, Single Row, 8 Circuits, with Solder Clips, Tin (Sn) Plating, Natural, Glow-Wire Capable	
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 8 Circuits, with Solder Clips, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable	1722872208
Ultra-Fit Vertical Header, 3.50mm Pitch, Single Row, 8 Circuits, with Solder Clips, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable	1722872308
Ultra-Fit Right-Angle Header with Solder Nail, 3.50mm Pitch, Single Row, 8 Circuits, Tin (Sn) Plating, Natural, Glow-Wire Capable, Tray	1723104108
Ultra-Fit Right-Angle Header with Solder Nail, 3.50mm Pitch, Single Row, 8 Circuits, 0.38µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray	1723104208
Ultra-Fit Right-Angle Header with Solder Nail, 3.50mm Pitch, Single Row, 8 Circuits, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray	1723104308
Ultra-Fit Plug Housing, 3.50mm Pitch, Single Row, 8 Circuits, Natural, Glow-Wire Capable	2025694008
Ultra-Fit Plug Housing, 3.50mm Pitch, Single Row, 8 Circuits, Panel Mount, Natural, Glow-Wire Capable	2025694108

Use with Part(s)

Description	Part Number
Ultra-Fit Connector Position Assurance (CPA) Retainer, UL 94V-0, Red	2171853000
Ultra-Fit Tangless Crimp Terminal, Female, 0.38µm Gold (Au) Plating,	1722536011

Downloaded from Arrow.com.

18-16 AWG	
Ultra-Fit Tangless Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 22-20 AWG	1722536111
Ultra-Fit Tangless Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 18-16 AWG	1722536012
Ultra-Fit Tangless Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 22-20 AWG	1722536112
Ultra-Fit Tangless Crimp Terminal, Female, Tin (Sn) Plating, 18-16 AWG	1722537023
Ultra-Fit Tangless Crimp Terminal, Female, Tin (Sn) Plating, 22-20 AWG	1722537123
Pre-Crimped Lead Ultra-Fit Tangless-Female-to-Ultra-Fit Tangless Female, Tin (Sn) Plating, 150.00mm Length, 16 AWG, Black	797582141
Pre-Crimped Lead Ultra-Fit Tangless-Female-to-Ultra-Fit Tangless Female, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black	797582142
Ultra-Fit Tangless Terminal Position Assurance (TPA), 3.50mm Pitch, 8 Circuits, Black	1722643008

Downloaded from Arrow.com.