




Part Number : [150250212](#)
Product Description : 0.40mm Pitch Premo-Flex FFC
Jumper with Latching Ears, Same Side Contacts (Type
A), 51.00mm Cable Length, Gold (Au) Plating, 120
Circuits
Series Number : 15025
Status : Active
Product Category : Flat-Flexible Cable (FFC)




Documents & Resources

Drawings
[150250212 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications
[150250001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15025
Description	0.40mm Pitch Premo-Flex FFC Jumper with Latching Ears, Same Side Contacts (Type A), 51.00mm Cable Length, Gold (Au) Plating, 120 Circuits
Product Name	Premo-Flex FFC Jumper
UPC	196823764004

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V AC

Physical

Cable Length	51.00mm
Circuits (Loaded)	120
Contact Layout Type	A (same side)
Design Feature	Superior Retention
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.40mm
Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector

Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC Connector, 0.40mm Pitch, FD4P Series, Right- Angle, Bottom Contact, 2.00mm Height, 120 Circuits, Gold over Nickel Plating	<u>2203631200</u>

This document was generated on Sep 11, 2025