

Product data sheet

Specifications



APC Replacement Battery Cartridge, VRLA battery, 5.1Ah, 192VDC, 2-year warranty

APCRBC140

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Replacement battery cartridge
Battery type	Lead-acid battery
Provided equipment	Battery recycling guide

Physical

Colour	Black
Height	12.2 cm
Width	19.7 cm
Depth	59.7 cm
Net weight	34.55 kg
Mounting mode	Not rack-mountable

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 % non-condensing
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 % non-condensing

Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cartridge
Battery voltage	192 V
Additional information	Each APCRBC140 consists of 2 battery modules as shown in the product image.

Number of battery replacement quantity	1
--	---

Replacement battery

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	22.6 cm
Package 1 Width	78.1 cm
Package 1 Length	40.9 cm
Package 1 Weight	37.27 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)