

## Data Sheet | Item Number: 211-836

Cable tie marker; for Smart Printer; for use with cable ties; 100 x 15mm; white

<https://www.wago.com/211-836>



Color: ■ white

### Technical data

Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	800 pcs/reel; 2 lines
Properties	Inner wrap (inside marking area)
Printing device	Smart Printer (thermal transfer printer)

### Physical data

Height	15 mm
Width	117.5 mm
Depth	0.17 mm
Marking surface	97 x 15 mm

### Mechanical data

Mounting type	Mounting with cable ties
Smear resistance	in conjunction with 258-5005 Ink Ribbon

### Material data

Color	white
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	600 g
Fire load	0 MJ

### Environmental requirements

Ambient temperature (storage)	+10 ... +21 °C
Ambient temperature (operation)	-30 ... +120 °C
Relative humidity	40 ... 50 %

### Commercial data

PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4055143040891
Customs tariff number	39269097900

### Product Classification

UNSPSC	55121612
eCl@ss 10.0	27-40-04-01
eCl@ss 9.0	27-40-04-01
ETIM 9.0	EC001530
ETIM 10.0	EC001530
ECCN	NO US CLASSIFICATION

### Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

### Downloads

#### Environmental Product Compliance

##### Compliance Search

Environmental Product  
Compliance 211-836



### Documentation

#### Operating Instructions

211-836 Information on  
printing material      1      28.08.2020      pdf  
1467.39 KB

