Part Number : 191930219
Product Description : VersaKrimp Ring Tongue Terminal for 6 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Carton
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : E-357-56



Documents and Resources

Drawings

191930219_sd.pdf

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 6 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755050707

Agency

CSA	LR18689
UL	E32244

Electrical

Voltage - Maximum	up to 35kV

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	5.135/g
Packaging Type	Carton
Plating min - Mating	2.540µm

Downloaded from Arrow.com.

Plating min - Termination	2.540µm
Stud Size	5/16" (M8)
Temperature Range - Operating	-50° to +149°C
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	6
Wire Size mm^2	16.00

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	192860117
Die Set (Large) for the HHLS Hydraulic Crimper	192900004
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	192940008
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	640013900
Square DIN Style Dies for 6 AWG	640037770
Crimp Head for the AT-200 Pneumatic Hand Tool	640074300
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	638162000

Downloaded from Arrow.com.