

Portable Charger - 2x USB-A, 12,000mAh Power Bank, Lithium-Ion, Auto Sensing, Black

MODEL NUMBER: UPB-12K0-S2X2U



Compact 2-port 12,000mAh power bank charges multiple smartphones, tablets, e-readers, MP3 players and other handheld mobile devices anywhere, anytime, without plugging into an AC power outlet.

Features

Travel-Sized for Convenient Charging of Devices Anywhere

- Compact form fits comfortably in your purse or backpack
- Ideal for charging up to 2 smartphones, tablets, e-readers, MP3 players and other handheld mobile devices simultaneously
- Works with Android, Apple and Windows devices

Built-In 12,000mAh Lithium-Ion Battery Charges Without an AC Power Outlet

- Charges at maximum power draw for hours to ensure your devices are ready when you need them
- Dual USB ports provide up to 5V 2.4A of power
- Auto-sensing ports adjust amperage to match amperage of connected device
- Protects against short circuits, overvoltage, overcurrent, overcharges and overdischarges

Easy to Recharge for the Next Time You Leave Home or Office

- USB Micro-B port connects to USB charger or computer's USB-A port to charge internal battery
- Built-in LEDs indicate at a glance how much battery capacity is left
- 3 ft. USB Micro-B charging cable included

Specifications

OVERVIEW	
UPC Code	037332203939
Product Type	Portable Charger
Charging Form Factor	Portable

Highlights

- Dual USB-A ports provide up to 5V 2.4A of power
- Auto-sensing port adjusts amperage to match connected device
- LEDs indicate remaining battery capacity at a glance
- 3-ft. (0.91 m) USB Micro-B charging cable included
- Compact form fits comfortably in your purse or backpack

Package Includes

- UPB-12K0-S2X2U 12,000mAh Dual-Port Mobile Power Bank USB Battery Charger
- USB Micro-B cable, 3 ft.
- Owner's manual

Device Compatibility	Phone; Tablet; Amazon Kindle
Country/Region	Global
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	USB MICRO-B (FEMALE)
Input Plug Type Details	USB-A to USB Micro B cable provided
OUTPUT	
Continuous Output Capacity (Watts)	12
Overload Protection	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	No
Capacity (Ah)	12
POWER	
USB Power Delivery (PD) Charging Support	No
CHARGING	
Number of Charging Ports	2
Total Charging Amps	2.4A
Total Charging Watts	12
Charging Method	USB
Charging Method Detail	12,000 mAh
Charging Port Type	(2) USB A (FEMALE)
Charging Ports	(2) 2.4A Quick Charge
Charging Ports Details	USB-A: 5V/2.4A
Charging Ports / Amps	(2) 2.4A
Magnetic Charging	No
Wireless Charging	No
Smart Charging Details	(x2) 5V 2.4A charging ports auto sense power draw needed from connected device
Compatible Devices	Portable Speaker; Smartphone; Tablet
Charging Amps per Port	2.4
PHYSICAL	
Color	Black

Material of Construction	ABS
Total Number of Ports	3
Unit Dimensions (hwd / in.)	5.500 x 2.500 x 1.000
Unit Dimensions (hwd / cm)	14 x 6.4 x 2.5
Unit Weight (lbs.)	0.60
Unit Weight (kg)	0.27
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	5° to 113°F (-15° to 45°C)
Relative Humidity	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MICRO-USB B (FEMALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
USB Hub Ports	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty