TE Connectivity: Every Connection Counts
© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

PLUGGABLE I/O CABLE ASSEMBLIES

✔ Active

PRODUCT DRAWING
English

TE CONNECTIVITY (TE)

C/A, INTERNAL HD MINI SAS, 100 OHM, R/A

2820328-3
TE Internal Number: 2820328-3

Always EU RoHS/ELV Compliant

Cable Assembly Type **Mini Serial Attached SCSI (Mini-SAS) HD**

Wire Size (AWG) **30**

Color **Black**

Flammability Rating **CL2**

Halogen Free **No**

Product Drawings	C/A, INTERNAL HD MINI SAS, R/A TO R/A 100 OHMS, 4X, HALOGENATED PDF **English**	

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Cable Assembly Type	**Mini Serial Attached SCSI (Mini-SAS) HD**
	Cable Style	**Madison TurboTwin - Composite Flat**
	Product Type	**Cable Assembly**
	Cable Assembly Category	**High Speed**
Configuration Features	Number of Positions	**8 Pair**
	Number of Signal Positions	**16**
	Configuration	**Double-Ended**
Electrical Characteristics	Impedance (Ω)	**100**
Signal Characteristics	Data Rate (Gb/s)	**12**
Body Features	Color	**Black**

Downloaded from Arrow.com.

Dimensions	Wire Size (AWG)	**30**
Operation/Application	Halogen Free	**No**
Industry Standards	Flammability Rating	**CL2**
Other	CLOUDSPLITTER	**No**
Product Compliance	Statement of Compliance PDF VIEW ALL PRODUCT COMPLIANCE	

Downloaded from Arrow.com.