

GQM2195C2A471FB12#

Note: This datasheet may be out of date.

Please download the latest datasheet of GQM2195C2A471FB12%23 from the official website of Murata Manufacturing Co., Ltd.

<http://www.murata.com/en-US/products/productdetail?partno=GQM2195C2A471FB12%23>

“#” indicates a package specification code.

In Production

General

RoHS

REACH

125 °C max.

High Q


Reflow OK

Flow OK

< List of part numbers with package codes >

GQM2195C2A471FB12D

Appearance & Shape



References

Packaging	Specifications	Minimum Order Quantity
D	180mm Paper Tape	4000

Mass (typ.)	
1 piece	9.5mg
φ180mm Reel	152g

1 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Note: This datasheet may be out of date.

Please download the latest datasheet of GQM2195C2A471FB12%23 from the official website of Murata Manufacturing Co., Ltd.

<http://www.murata.com/en-US/products/productdetail?partno=GQM2195C2A471FB12%23>

“#” indicates a package specification code.

Specifications

Length	2.0±0.15mm
Width	1.25±0.15mm
Thickness	0.85±0.15mm
Capacitance	470pF ±1%
Distance between external terminals g	0.7mm min.
External terminal size e	0.2 to 0.7mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	100Vdc
Size code in inch(mm)	0805 (2012M)
TC	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

2 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.