

Universal Reversible USB 2.0 Adapter (Reversible A to Right-Angle A M/F)

MODEL NUMBER: **UR024-000-RA**



Highlights

- Universal / Reversible A-Male plugs in any direction
- Turns a standard USB cable into a Universal Cable
- Right-Angle A connector ideal in situations where space is at a premium
- USB2.0 Rated

Package Includes

- Universal Reversible USB 2.0 A-Male to Right-Angle A-Female Adapter

Turn your standard USB cable into a Universal Cable

Description

Tripp Lite's UR024-000-RA, USB Male to Female adapter, features a Universal / Reversible Male end which allows the adapter to be plugged in any direction on a computers USB port. Add this adapter to a standard USB cable, and convert it to a Universal pluggable cable. The Right-Angle A connector is ideal in situations where space is at a premium. USB2.0 rated for 480mbps transfer rates. Fully molded, with gold plated contacts for a lifetime of use.

Features

- USB 2.0 Male-to Female adapter, with Universal / Reversible Male connector
- Male end can be plugged in any direction
- Right-Angle A connector ideal in situations where space is at a premium
- USB2.0 Hi-Speed rated

Specifications

OVERVIEW	
UPC Code	037332182913
Technology	USB 2.0 (High Speed)
PHYSICAL	
Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	0.05 x 4.50 x 7.00

Shipping Dimensions (hwd / cm)	0.13 x 11.43 x 17.78
Shipping Weight (lbs.)	0.05
Shipping Weight (kg)	0.02
Unit Dimensions (hwd / in.)	0.690 x 1.380 x 0.790
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty