

Product data sheet

Specifications



APC Notebook Surge Protector for AC, phone and network lines, 2 pin connection, 100-240V

PNOTEPROC8

❗ Discontinued on: 15 October 2021

❗ End-of-service on: 15 October 2021

❗ Discontinued

PNOTEPROC8 has not been replaced. Please contact your customer care center for more information.

Overview

Lead time Usually in Stock

General

Provided equipment 2 x 1.8 m telephone cables
30 cm network patch cable
Cord management straps
User manual

Physical

Colour Silver
Depth 9.8 cm
Height 2.7 cm
Net weight 0.1 kg
Width 3.2 cm

Input

Input power 300 W
Maximum line current 4 A
Network frequency 50/60 Hz
Plug standard IEC 60320 C8
Input voltage 120 V

Output

Number of power socket outlets 1
Outlet standard IEC 60320 C8

Conformance

UL 1449 TVSS rating 700
Product certifications CSA
NOM
UL listed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	FCC part 68
Equipment protection policy	Lifetime : \$75000

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...9144.00 m

Surge Protection and Filtering

Response time	1 ns common mode
Common mode rejection	0 dB
Peak current	0 kA common mode 6.5 kA normal mode
Surge energy rate	180 J
Data line protection	RJ11 modem/fax protection (two wire single line) RJ45 10/100 Base-T Ethernet protection

Packing Units

Package 1 Weight	0.2 kg
Package 1 Height	6.6 cm
Package 1 width	15.8 cm
Package 1 Length	19.2 cm
SCC14	10731304220722
Number of Units in Package 2	12
Package 2 Weight	2.72 kg
Package 2 Height	210.82 mm
Package 2 width	292.10 mm
Package 2 Length	419.10 mm
Number of Units in Package 3	480

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------