Part Number : 1210503398
Product Description : mPm DIN Valve Connector, Form C - 8mm, 2 Pole Plus Ground, to 5.0m (16.40') PUR UL Cable Pigtail, Yellow LED, Black Nitrile Gasket, 115V
Series Number : 121050
Status : Obsolete
Product Category : Industrial Cable Assemblies
Engineering Part Number : E492B2A50011S0L



Documents and Resources

Drawings

1210503398_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Obsolete

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Industrial Cable Assemblies
Series	121050
Description	mPm DIN Valve Connector, Form C - 8mm, 2 Pole Plus Ground, to 5.0m (16.40') PUR UL Cable Pigtail, Yellow LED, Black Nitrile Gasket, 115V
IP Rating	IP65
Product Name	mPm
Protocol	N/A
Type	Single Ended
UPC	78172534610

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	115V

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Brad mPm DIN C - 8mm
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	Yellow
Material - Cable Jacket	PUR UL
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A

Obsolete

Downloaded from Arrow.com.

Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	20

Obsolete

Downloaded from Arrow.com.