
ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	NOTES
1	50-00011	Connector, dc plug, 5.5x2.5xBL7.5xL30 locking style, brass nickel plated, threaded nut 5/16-32	1	
2	30-00415	Wire, 2C TS, 18 AWG, UL2468, 300V, 80°C, 4.4 mm, VW-1, PVC, red and black	1	
3	24-00016	Overmold, PVC, black	1	



Notes:
Cable rated for 48 V, 6.5 A

Hi-Pot test: 600 Vac, 0.5 mA, 1 second

Wiring Diagram	
50-00011	wire color
center	red
sleeve	black

Revision:	Date:	Description:
A	11/2/2022	Initial release

Prepared: MP Digitally signed by MP Date: 2022.11.10 08:27:56 -08'00'

Verified: JD Digitally signed by JD Date: 2022.11.10 14:39:03 -08'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:

RoHS compliant

Function test: no open, no short circuit, no intermittent

Description:

Cable, 4000 mm, 5.5x2.5x7.5mm 50-00011 locking dc plug to 5mm tinned, 18 AWG, UL2468, 30-00415, r&b

TENSILITY

tel 1.541.323.3228 *800* 877.670.7118
fax 1.541.323.4202 *web* tensility.com

Size: A

Part number: 10-05243

Scale: 1:1

Sheet 1 of 1

To see a custom version of this cable assembly, call Tensility at 541-323-3228 or email engineering@tensility.com

5 4 3 2 1

Downloaded from Arrow.com.