

Part Number : 1300950283
Product Description : Multi-Weave Wire Mesh Pulling Grip, Rotating Eye, Mesh Length 1.524m (60.00"), Approximate Break Strength 13879.93kg (30600 lbs)
Series Number : 130095
Status : Obsolete
Product Category : Cable Grips
Engineering Part Number : 36625

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Multi-Weave Wire Mesh Pulling Grip, Rotating Eye, Mesh Length 1.524m (60.00"), Approximate Break Strength 13879.93kg (30600 lbs)
Comments	Color Identifier Red
Product Name	Multi-Weave
Type	Pulling Grip
UPC	78678836625

Agency

CSA	LR32159

Physical

Approximate Break Strength	13879.93kg (30600 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	38.10-44.20mm (1.500-1.740")
Color - Grommet	N/A
Eye Diameter	1 7/8"
Eye Type	Rotating
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	1.524m (60.00")
Net Weight	2058.701/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Obsolete

Downloaded from Arrow.com.