Part Number : 1200945027
Product Description : Brad M23 Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 22-18 AWG, PUR Cable, 5.0m (16.40') Length
Series Number : 120094
Status : Obsolete
Product Category : Industrial Cable Assemblies
Engineering Part Number : K03001P80M050

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Industrial Cable Assemblies
Series	120094
Description	Brad M23 Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 22-18 AWG, PUR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Brad M23
Protocol	N/A
Type	Single Ended
UPC	883906319625

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	63V AC/DC

Physical

Cable Diameter	11.43mm (.450")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	M23
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	None
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold

Obsolete

Downloaded from Arrow.com.

Net Weight	348.478/g
Orientation	90° to Pigtail
Poles	19
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	N/A
Wire Size (AWG)	18, 22

Obsolete

Downloaded from Arrow.com.