




Pos.4

Pos.1

P1

1

2

25.0±5.0

6

4

LABEL

L

2

3

5

7

9

10

11

12

Pos.1

Pos.5

P2

25±5

35±2

13±2

YYWW

MADE IN CHINA

Clear

LABEL DETAIL

NOTES:

1. 100% ELECTRICAL TEST.

2. PACKAGE: 1PCS/PE BAG.

3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.

PIN ASSIGNMENT :

P1

2

3

1

4

Shell

Pair 1

White(D-)

Green(D+)

Red(V BUS)

Black(Gnd)

Drain

Braid

P2

2

3

1

5

Shell

OBSOLETE

-	-	-	-	-	AR	AR	MR	UL TAPE, W: 9MM, COLOR: BLACK	12
1	-	-	-	-	-	-	PC	CONNECTOR,MINI USB B TYPE	11
-	-	-	-	1	1	1	PC	CONNECTOR,MINI USB B TYPE	10
AR	AR	AR	AR	AR	AR	AR	MR	Heat Shrink Tubing 1.0MM BLACK	9
AR	AR	AR	AR	AR	AR	AR	MR	Copper Foil, W: 5.0MM	8
-	AR	AR	-	-	-	-	MR	Heat Shrink Tubing, 1.5mm, Color: Black	7
-	-	-	-	-	AR	MR	PVC TUBE, ID: 1.5MM, COLOR: BLACK		
AR	-	-	AR	AR	-	MR	Heat Shrink Tubing, 1.0mm, Color: Black		
1	1	1	1	1	1	1	PC	LABEL , 25*35mm.	6
AR	AR	AR	AR	AR	AR	AR	MR	Copper Foil, W: 10.0MM.	5
AR	AR	AR	AR	AR	AR	AR	MR	USB 2.0 Cable, 1P(Signal)+2C(Power)+Al/Mylar +Drain+Braid, Color: Black.	4
-	1	1	-	-	-	-	PC	Mini USB, B PLUG, SOLDER TYPE	3
AR	AR	AR	AR	AR	AR	AR	KG	Overmolded PVC,Color: Black(BK01).Shore A 80±5	2
1	1	1	1	1	1	1	PC	USB A Type Solder Contacts: Gold Plated 30U”	1
-6	-5	-4	-3	-2	-1	U/M		Shell: Nickel Plated, Insulation: White	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN

BOVEY LIU

28/JUN/01

CHK

BEVIN

28/JUN/01

APVD

MARK

28/JUN/01

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

CABLE ASSY, MINI USB B TYPE TO USB A TYPE

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=1496476

RESTRICTED TO

-

SCALE

N.T.S.

SHEET

1 OF 1

REV

U3

1471-9 (3/11)

Downloaded from Arrow.com