







52S + 5P	6450882-5
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO THE TERMS AND CONDITIONS OF THE DRAWING ORGANIZATION AND SHOULD BE CONTROLLED FOR THE LATEST REVISION.				DWN C_ZHOU 31MAR2009 CHN S_ZHAO 31MAR2009 APVD S_YAO		 Tyco Electronics Shanghai, P.R.China, 200233	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.01 1 PLC ±.01 2 PLC ±.01 3 PLC ±.005 4 PLC ±.0020 ANGLES ±.7°		NAME INVERTED RIGHT ANGLE RECEPTACLE AND SHORT END MODUAL MULTI-BEAM XLE		SIZE A	
		FINISH 2 3		PRODUCT SPEC 108-2292 APPLICATION SPEC 114-13038		CAGE CODE 00779	
MATERIAL 2		WEIGHT -		DRAWING NO C6450882-5		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 2	
						REV A5	

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

PART NUMBER	ROWS		SIGNAL													POWER					
			1	2	3	4	5	6	7	8	9	10	11	12	13	P1	P2	P3	P4	P5	
6450882-5	A		A	A	A	A	A	A	A	A	A	A	A	A							
	B		B	B	B	B	B	B	B	B	B	B	B	B							
	C		C	C	C	C	C	C	C	C	C	C	C	C						C	
	D		D	D	D	D	D	D	D	D	D	D	D	D						D	
52S + 5P																					



STD PRESS FIT SIGNAL CONTACT, .119 TAIL LENGTH, ROW D	D
STD PRESS FIT SIGNAL CONTACT, .119 TAIL LENGTH, ROW C	C
STD PRESS FIT SIGNAL CONTACT, .119 TAIL LENGTH, ROW B	B
STD PRESS FIT SIGNAL CONTACT, .119 TAIL LENGTH, ROW A	A
MFBL PRESS FIT POWER CONTACT, .119 TAIL LENGTH	RP
STD PRESS FIT POWER CONTACT, .119 TAIL LENGTH	RS
DESCRIPTION	
IDENTIFIER	

DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN C. ZHOU 31MAR2009		Tyco Electronics ShangHai, P.R.China. 200233	
		9 PLC ±.01 2 PLC ±.01 5 PLC ±.005 4 PLC ±.0020 ANGLES ±.2°		CHK S. ZHAO 31MAR2009		NAME INVERTED RIGHT ANGLE RECEPTACLE AND SHORT END MODUAL MULTI-BEAM XLE	
MATERIAL -		FINISH -		APVD S. YAO		PRODUCT SPEC 108-2292	
				APPLICATION SPEC 114-13038		SIZE A1100779	
				WEIGHT -		CAGE CODE C=6450882-5	
				CUSTOMER DRAWING		RESTRICTED TO -	