

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)

[Home](#) / [Products](#) / [M Series](#) / [M12 \(A\)](#)

Product Line

- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- Accessory
- M5
- Guided M8
- M8
- M10.5
- M12 (A)
- M12 (B)
- M12 (D)
- M12 (I)
- M12 (K)
- M12 (L)
- M12 (S)
- M12 (T)
- M12 (V)
- M23
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



M12A-12PFFS-SF8B15

- Operating Temperature: -20°C ~ +85°C
- Transmission Speed: N/A
- Shielded: Metal, Non-shielded
- Jacket Material: PVC
- Certificate: UL1977, UL2238, UL1863

You must login first to view the price

Quantity

- 1 +

- Add to Cart
- Inquiry
-

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Receptacle With Wires
Shielded Metal, Non-shielded	No. of Contacts 12
Connector Gender Female	Backshell Hexagonal
Mating Style Screw Thread	IP Rating IPX8
Assembly Style Solder	
<div> More Options</div>	

People Also Bought