

Representative Image

Catalog No. TC1104

Description: 4 BUNDLE MNTG STRIP 5.5X.5IN NAT NY

UPC No 5414363057970

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Multiple Bundle Mounting Strip, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 139mm (5.5 Inches), Width of 12.7mm (0.50 Inch), Thickness of 3.17mm (0.125 Inch), Two-Screw Mounting Method, #6 Screw, Maximum Tie Width 4.82mm (0.19 Inch)

Descriptors

Category	Cable tie mounts
Special Features	These nylon mounting strips for parallel installation of wire bundles can accommodate up to six closely spaced bundles.

Specifications

Cable Size	0.19 in , 4.82 mm
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	139 mm
Length	5.5 inch
Width	12.7 mm
Width	0.5 inch
Suitable for cable tie width to	4.82 mm
Suitable for cable tie width to	0.19 inch
Type of fastening	Other

by ABB

Downloaded from Arrow.com.

ETIM	EC000449 Mounting base and -element for cable ties
Diameter mounting hole	3.71 mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.