Note: This datasheet may be out of date.

Please download the latest datasheet of SCA830-D06 from the official website of Murata

Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=SCA830-D06

# SCA830-D06












## Appearance & Shape







## **Packaging Information**

Packaging	Specifications	Standard Packing Quantity
-1	330mm Embossed Tape	100

1 of 2

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



# SCA830-D06

Note: This datasheet may be out of date.

Please download the latest datasheet of SCA830-D06 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=SCA830-D06



# **Specifications**

Output Type	SPI	
Axis	1	
Maximum Range	±2g	
Supply Voltage	3.3V	
Offset Temp. Characteristc	±30mg	
Amplitude Response	50Hz	
Mass	0.31g	

2 of 2

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

