


APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/11/05	
A		REDRAWN	9/26/11	
B		REDRAWN	6/3/14	AY/YC
C		UPDATE DIM.	10/19/15	AY/GC



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Ivory

Latch: PA66, rated UL 94V-0, color: Ivory

Contacts: Copper Alloy

Shell: SPCC, Nickel plated

Boardlock: SPCC, Tin plated

Plating:

Gold flash over Nickel underplate on mating area,

Tin over Copper underplate on tails

Electrical:

Operating voltage: 40 VAC max

Current rating: 1.5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min


Dielectric withstanding voltage: 500 VDC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010		APPROVALS		DATE		TITLE		SIZE		PART NO.		REV.	
DRAWN		SS		5/11/05		DIGITAL VIDEO INTERFACE SOCKET		X		DVI-SL-24-2		C	
CHECKED						RIGHT ANGLE, PCB TAILS, ANALOG							
APPROVED						REF: S00027T		SCALE: NTS		SHEET 1 OF 1			

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

DIGITAL VIDEO INTERFACE SOCKET
RIGHT ANGLE, PCB TAILS, ANALOG

SIZE	PART NO.	REV.
X	DVI-SL-24-2	C
REF: S00027T	SCALE: NTS	SHEET 1 OF 1