

Specifications

Eaton 182930

Eaton Moeller® series M30 Illuminated pushbutton actuator, RMQ-Titan, Flat, momentary, White, inscribed 1, Metal bezel

General specifications

PRODUCT NAME	Eaton Moeller® series M30 Illuminated pushbutton actuator
CATALOG NUMBER	182930
MODEL CODE	M30C-FDL-W-X1
EAN	4015081778577
PRODUCT LENGTH/DEPTH	36 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	46 mm
PRODUCT WEIGHT	0.041 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660 CSA File No.: 012528 CSA Class No.: 3211-03 DNV UL File No.: E29184 GL IEC/EN 60947-5 UL 508 CSA-C22.2 No. 14-05 and 94-M91 CE marking UL Category Control No.: NKCR UL Listed CSA certified
GLOBAL CATALOG	182930

Product specifications

TYPE	Illuminated pushbutton actuator
ACTUATOR COLOR	White
FEATURES	Labelled
ACTUATOR FUNCTION	Spring-return Momentary
FITTED WITH:	Front ring
OPERATING FREQUENCY	3600 Operations/h
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
ACTUATING FORCE	5 N
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
FORCE FOR POSITIVE OPENING - MIN	0 N
NUMBER OF COMMAND POSITIONS	1
OPENING DIAMETER	30.5 mm
OPENING HEIGHT	0 mm
BEZEL COLOR	Titanium
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
BEZEL MATERIAL	Metal
DESIGN	Flat Flat front
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP69K IP67 IP66
DEGREE OF PROTECTION (FRONT SIDE)	IP67/IP69K NEMA 4X, 13
INSCRIPTION	Inscribed
FRONT ELEMENT TYPE	Flat
LENS TYPE	Round

Resources

CATALOGS

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[Flip catalog - Product Range Catalog - Command and indication](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

DECLARATIONS OF CONFORMITY

[DA-DC-00004135.pdf](#)

[DA-DC-00004157.pdf](#)

[eaton-operating-m30-dimensions-004.eps](#)

[eaton-operating-m30-dimensions.eps](#)

[eaton-operating-m30-dimensions-005.eps](#)

[eaton-operating-m30-dimensions-006.eps](#)

[eaton-general-m22-symbol.eps](#)

[eaton-general-approval-m22-symbol.eps](#)

[eaton-operating-m30-3d-drawing.eps](#)

[116C090](#)

ECAD MODEL

[ETN.182930.edz](#)

FLYERS

[eaton-rmq-titan-selection-aid-brochure-fl047002-en-us.pdf](#)

INSTALLATION INSTRUCTIONS

[eaton-operating-devices-m30-rmq-titan-flat-front-instruction-leaflet-il047019zu.pdf](#)

INSTALLATION VIDEOS

[RMQ Flat Design](#)

MCAD MODEL

[DA-CD-drucktaste flach flatfront](#)

[DA-CS-drucktaste flach flatfront](#)

LIFESPAN, MECHANICAL	5,000,000 Operations
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ-Titan
SIZE	Front dimensions: Ø 36 mm
SUITABLE FOR	Illumination

MULTIMEDIA

[easyE4 SmartWire-DT module with Remote Touch Display and RMQ multi color indicator](#)

[RMQ small E-Stop emergency-stop button](#)

[MCI MultiColor Light Indicator RMQ compact solution](#)

[MCI Multicolor Light Indicator M22 with SmartWire-DT](#)

SALES NOTES

[eaton-rmq-mci-multi-color-light-indicator-flyer-fl047005en-en-us.pdf](#)

[eaton-rmq-small-e-stop-flyer-fl047006en-en-us.pdf](#)

[eaton-rmq-flat-enclosure-flyer-fl047003en-en-us.pdf](#)

[eaton-control circuit-devices rmq-titan-fl144090en-en-us.pdf](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.