
**Part Number :** 464369204
**Product Description :** EXTreme Ten60Power Right-Angle Receptacle without Guides, 4 DC Power Circuits, Press Fit Tail
**Series Number :** 46436
**Status :** Active
**Product Category :** Board-to-Board Connectors
**Engineering Part Number :** 046436-9204




## Documents and Resources

### Drawings

464369204_sd.pdf

PK-46436-001-000.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

AS-46436-100-001.pdf

PS-46436-100-001.pdf

464361000-TS-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Board-to-Board Connectors |
| Series | 46436 |
| Description | EXTreme Ten60Power Right-Angle Receptacle without Guides, 4 DC Power Circuits, Press Fit Tail |
| Application | Board-to-Board |
| Comments | See Product Specification for details |
| Component Type | Receptacle |
| Keyword | Ten60 |
| Product Name | EXTreme Ten60Power |
| UPC | 193264043958 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 60.0A |

Downloaded from Arrow.com.

| | |
|---|---|
| Voltage - Maximum | 600V AC / 250V DC |

**Physical**

| | |
|---|---|
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Black |
| Durability (mating cycles max) | 200 |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | No |
| Lock to Mating Part | No |
| Mated Height | 10.00mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Matte Tin |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 11.851/g |
| Number of Rows | 1 |
| Orientation | Right Angle |
| Packaging Type | Tray |
| PCB Locator | No |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.58mm |
| PC Tail Length | 3.28mm |
| Pitch - Mating Interface | 5.50mm |
| Plating min - Mating | 0.762µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| (p)ower-(s)ignal Configuration | 4p - 0s |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Through Hole - Compliant Pin |

Downloaded from Arrow.com.

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
| --- | --- |
| EXTreme Ten60Power Right-Angle Plug without Guides, 4 DC Power Circuits,  Press Fit Tail | 464379204 |



Downloaded from Arrow.com.