



C2G
125ft (38.1m) Cat6 Snagless Unshielded (UTP) Ethernet Network Patch Cable - Blue
Part No. 27148



For fast Ethernet and Gigabit computer networks that require bandwidth-intensive voice, data, or video distribution applications. Meets all Cat6 TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL). Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

Features & Benefits

Snagless design protects clips when plugging and unplugging

Standard RJ45 connectors and unshielded twisted pair wires

Available in 10 colors to color-code a network

Available in lengths up to 150ft

Specifications

General Info

| | | | |
|---------------|---------------------------|--------------------|-------------------------------------|
| Product Line | C2G | Color | Blue |
| UPC Number | 757120271482 | Country Of Origin | Vietnam |
| Features | PoE (Power Over Ethernet) | Application Sector | Commercial, Industrial, Residential |
| Warranty Type | Lifetime | Type | Cable |

Dimensions

| | | | |
|-------------------|----------|--------------|--------|
| Product Length US | 125.0 FT | Cable Length | 125 ft |
| Outside Diameter | 5.69 mm | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|--------------|-----|-----------------|-----|
| CE Certified | Yes | REACH Compliant | Yes |
|--------------|-----|-----------------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|---------------------------|--------------------------|----------------------------------|----------------------|
| Jacket Material | PVC (Polyvinyl Chloride) | Category Performance Application | Cat6 |
| Wiring Scheme | T568B | Wire Gauge | 24 AWG |
| Shielded/Unshielded Cable | Unshielded | Shield Type | UTP |
| Cable Type | Ethernet Patch Cable | Jacket Rating | Standard / Non-Rated |
| Cable Diameter | 6.2 mm | Connector Type | Booted, Snagless |
| Indoor/Outdoor | Indoor | Connector 2 | RJ-45 Male |
| Connector 1 | RJ-45 Male | | |
