








PRODUCT NO.
10122822-001RLF



RECOMMENDED PCB LAYOUT
THICKNESS=1.1mm (TOLERANCES ±0.05)



NOTES:

- MATERIAL:
 - HOUSING: HIGH THERMOPLASTIC RESIN, UL94V-0, COLOR: BLACK
 - CONTACT: COPPER ALLOY
 - CAP: HIGH THERMOPLASTIC RESIN, UL94V-0, COLOR: BLACK
 - NUT: COPPER ALLOY
- FINISH:
 - CONTACT: GOLD PLATING ON CONTACT AREA
TIN(MATTE) PLATING ON SOLDER TAIL AREA
NICKEL UNDER PLATED OVERALL
 - NUT: NICKEL UNDER PLATED OVERALL
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS DESCRIBED IN GS-47-0004.
- RECOMMENDED SCREW TORQUE IS 1.5KGF-CM.

4. PART NUMBER DESCRIPTION:
10122822- 0 0 X X LF

CONTACT PLATING
1: Au 15u"
ROHS COMPLIANT
PACKING
R: TAPE AND REEL

5. APPLICABLE PRODUCT SPEC.: GS-12-1137
APPLICABLE PACKAGE SPEC.: GS-14-2309

mat'l. code				surface	tolerance	projection	product family	
				ASME Y14.5	ASME Y14.5		Series ATA	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
A		TAI	2013-04-26	angles	.X±0.35	MM	SATA Receptacle	
B	ELX-T-15098	TAI	2013-07-01	enr	.XX±0.25		High Rise R/A SMT	
C	ELX-T-15625	TAI	2013-08-26	chr	.XXX±0.15	scale	dwg no	
				appd	PM ZHENG	2013-05-06	sheet 1 of 1	
sheet index		revision	C				10122822	
		sheet	1				A4	
							CUSTOMER Drawing	

