

	1	2	3	4	5	6	7	8
A								
B								
C	27	33614311000002	Fiber optic, multi mode 50/125 µm	100				
	26	33614310900002		90				
	25	33614310800002		80				
	24	33614310700002		70				
	23	33614310600002		60				
	22	33614310500002		50				
D	21	33614310450002		45				
	20	33614310400002		40				
	19	33614310350002		35				
	18	33614310300002		30				
	17	33614310250002		25				
	16	33614310200002		20				
	15	33614310150002		15				
	14	33614310140002		14				
	13	33614310130002		13				
	12	33614310120002		12				
	11	33614310110002		11				
E	10	33614310100002		10				
	9	33614310090002		9				
	8	33614310080002		8				
	7	33614310070002		7				
	6	33614310060002		6				
	5	33614310050002		5				
	4	33614310040002		4				
	3	33614310030002		3				
	2	33614310020002		2				
F	1	33614310010002		1				
	Cont. no.	Part no.	Type of cable	Dim. a[m]				



HARTING Customised Solutions
D-32339 Espelkamp

All rights reserved
Department HCS - RO

All Dimensions in mm

Created by
COSTEA

Inspected by
COSTEA

Standardisation
MUNTEANV

Date
2018-07-19

State
Final Release

Title
FO CA PP2-LCdx, 50µ, OM3, PUR

Type
TB

Number
3361431XXX0002

Doc-Key / ECM-Nr.
100677880/UGD/009/D
500000137839

Rev.
D

Page
2/2

Tech. Character.

Free size tol.

According to production drawing