650V 18A Field Stop Trench IGBT - RGW50TK65 (New Product)

The datasheet is coming soon.

Package



VIEW

* This product is a standard grade product. This product is not recommended for use in car equipment.

購買 *

FAQ

CONTACT US

MAIN SPECIFICATION

TECHNICAL DATA

PART NO. | RGW50TK65GVC11

STATUS| SUPPLY

PACKAGE | TO-3PFM

NUMBER OF UNITS | 450

MINIMUM PACKAGE QUANTITY | 450

PACKING FORM | TUBE

Downloaded from Arrow.com.

ROHS | YES

SPECIFICATION:

Series	W: High speed fast SW
IN $_{CES}$ [V]	650
I_C(100°C)[A]	18
V $_{CE\ (sat)}$ (Typ.) [V]	1.5
tf(Typ.) [ns]	53
BV $_{CES}$ (Min.) [V]	650
Storage Temperature (Min.)[°C]	-55
Storage Temperature (Max.)[°C]	175

FEATURES:

N/A

RELATED PRODUCTS

Other new/current related products RGW50TK65

PART NUMBER	Datasheet
RGT20NL65D	-
Product Series: 650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	
查詢	

PART NUMBER	Datasheet
RGT20NS65D(LPDS)	-
Product Series: 650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	
查詢	

Downloaded from Arrow.com.

PART NUMBER
RGWX5TS65

Datasheet
-

Product Series
650V 75A Field Stop Trench IGBT for the High-Speed Fast Switch

查詢

PART NUMBER
RGWX5TS65D

Datasheet
-

Product Series
650V 75A Field Stop Trench IGBT for the High-Speed Fast Switch

查詢

PART NUMBER
RGT20NS65D(TO-262)

Datasheet
-

Product Series
650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)

查詢

PART NUMBER
RGT20TM65D

Datasheet

Product Series
650V 10A Field Stop Trench IGBT

查詢

NEW PRODUCT LIST

Downloaded from Arrow.com.