Part Number : 1300680069
Product Description : BradPower D-Size (1 3/8"–M35) 4-Pole Reducing Tee, with 4-Pole BradPower A-Size (7/8"–M22) Drop, Gray
Series Number : 130068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : TC40140-200



Documents and Resources

Drawings

1300680069_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130068
Description	BradPower D-Size (1 3/8"–M35) 4-Pole Reducing Tee, with 4-Pole BradPower A-Size (7/8"–M22) Drop, Gray
IP Rating	IP67
Product Name	BradPower D-Size
Type	Power Tap Tee
UPC	78172553868

Agency

UL	E258922

Electrical

Current - Maximum per Contact	15.0A, 25.0A
Voltage - Maximum	600V AC/DC

Physical

Drop Connector	BradPowerA-Size (7/8"–M22)
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	BradPower D-Size (1 3/8"–M35)
Left Trunk Gender	Female
Leg 1 Length	N/A

Downloaded from Arrow.com.

Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PVC
Material - Coupling Nut	Anodized Aluminum
Net Weight	444.000/g
Poles	4
Right Trunk Connector	BradPower D-Size (1 3/8"–M35)
Right Trunk Gender	Male
Temperature Range - Operating	-20° to +90°C

Downloaded from Arrow.com.