

Part Number : [2032635480](#)

Product Description : Sentrality 8.00mm Surface Mount Pin, 36.00mm Engagement Length, Bag

Series Number : 203263

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2032635480_sd.pdf](#)

[2032630006-PK-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[2043130001-AS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	203263
Description	Sentrality 8.00mm Surface Mount Pin, 36.00mm Engagement Length, Bag
Application	Board-to-Board, Busbar-to-Board, Busbar-to-Busbar
Component Type	PCB Header
Product Name	Sentrality
UPC	196823130410

Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	8.00mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Gender	Male

Glow-Wire Capable	No
Guide to Mating Part	No
Height Above Board	36.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	15.880/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Retention	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Top-entry Surface Mount Socket Assemblies	<u>204318</u>
Sentrality Top-entry Surface Mount Socket Assemblies with Self-alignment Capability	<u>204365</u>
Sentrality Top-entry Knurled Press-Fit Socket Assemblies with Self-alignment Capability	<u>204313</u>
Sentrality Top-entry Knurled Press-Fit Socket Assemblies	<u>204316</u>
Sentrality 3.40mm Right-Angle Socket Assemblies	<u>205000</u>

This document was generated on May 20, 2026