Loading...

Netguard 10-Outlet Rackmount Surge Strip

Rackmountable for the standard 19-inch configuration

★★★★★
0 Reviews

Product # : 27368

Roll over image to zoom in

In Stock, only 2 left

1
Add

Need it shipped today?
Place your order before the timer runs out!
01: 55: 18

print share chat

Product Info | Customer Reviews | Questions & Answers | Distributors

Description | Specs

Product Description

This surge strip protects your networking devices against destructive power line surges and data interference that may invade your office; easy to implement in the standard 19-inch configuration.

WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Specifications

Color :	Black
UPC :	757120273684
Warranty :	1 Year
Vendor :	C2G
Weight :	5.690 LB

- Power Source: 100 - 120 VAC 50/60 Hz
- Maximum Output Power Rating: 15 A
- Power Rating: 1800 VA
- Surge Protector Energy Rating: 1072 Joules (8 metal oxide varistors)
- Clamping Voltage: 330 VAC
- Maximum Spike Capacity: 52000 A
- Fax/Modem Surge Protector: RJ11 6P4C 19.8 Joules, Pin 3 to Pin 4
- Ethernet Surge Protector: Clamping Voltage 6.8 Vrms, 1007 µs, 300 W

Downloaded from Arrow.com.

- Modes Protector: Line to Neutral, Line to Ground, Neutral to Ground
- EMI/RFI Noise Filtration: 99% Removed from 100 kHz to 1 MHz
- Response Time: Instantaneous ([<(><<)>] 1 ns)
- Overload Protector: Overload 200%, 4 - 10 seconds
- Enclosure: Metal Housing 1U size
- Operating Temperature: 0 to 60°C
- Storage Temperature: -10 to 60°C
- Humidity: 0 to 95% (non-condensing)
- Power Cord Length: 3 meters

Norton SECURED powered by VeriSign

United States | Europe +

Copyright © 2019 C2G. All Rights Reserved

legrand®

Downloaded from Arrow.com.