



## MICRO D

HOME > PRODUCTS > HIGH REL > MICROD > PRODUCT DETAILS

### C115366-9227C

### MDM JACKPOST SERIES

### MDM JACKPOST



Image shown represents the product series and may not indicate the actual part number



#### TOOLBOX

[Product Selection Guide](#)  
[Sales Locator](#)



#### DOWNLOADS

[Datasheet](#)

CONTACT TECH SUPPORT

SEARCH DISTRIBUTOR STOCK

REQUEST SAMPLE

#### FEATURES AND BENEFITS

- Female screw lock for MDM Connectors
- Flight and Engineering models available
- Standard panel, Savers and Feedthrough
- Non-outgassing
- Order 1 part-numbers per connector

#### TYPICAL APPLICATIONS

- Space equipments
- Satellites harnesses and payloads
- Launchers
- Engineering
- Military and Avionics

#### ASSOCIATED PRODUCTS

- [MDM Connector](#)
- [MDMA Connectors](#)

#### SPECIFICATIONS

**Torque value - Standard - Male Side:** 0.44 Nm min / 0.48 Nm max

**Torque value - Standard - Female Side:** 0.28 Nm min / 0.32 Nm max

**Torque value - FR136/FR139 - Male Side:** 0.44 Nm min / 0.48 Nm max

**Torque value - FR136/FR139 - Female Side:** 0.28 Nm min / 0.32 Nm max

**Torque value - Savers - Male Side:** 0.36 Nm min / 0.40 Nm max

**Torque value - Savers - Female Side:** 0.28 Nm min / 0.32 Nm max

**Temperature range:** -55°C to 125°C

#### C115366-9227C

**Description:** MDM-115366-9227C

**Quality Level:** According to ESCC Specification

**Number of Contacts:** Not Applicable

**Contact Type:** Not Applicable

**Wire Size:** Not Applicable

**Finishing Option:** Not Applicable

|                          |                      |
|--------------------------|----------------------|
| <b>Termination Type:</b> | Not Applicable       |
| <b>Wire Length:</b>      | Not Applicable       |
| <b>Cable Type:</b>       | Not Applicable       |
| <b>Outlet:</b>           | Not Applicable       |
| <b>Shell Finish:</b>     | Not Applicable       |
| <b>Application:</b>      | FR136/FR139 versions |
| <b>Panel Mounting:</b>   | Rear Mounting        |
| <b>Panel Thickness:</b>  | 1.6mm                |
| <b>Nut Type:</b>         | NA                   |

We use cookies to provide our customers with an optimal site experience. View our [Privacy Policy](#) to learn more about how we use cookies and how to manage your settings. By proceeding on our website, you consent to the use of cookies. [Yes](#) [No](#)