








Max. Temperature: 260°C during 10 seconds									Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-SUB Low Profile 37p Male Right angled SMT with die casted grounds and 4-40 UNC nuts	Maßstab/ Scale 1,4:1	
								Detail.	29Sep2010	ED				
								Insp.						
								Stand.						
09554663816.741	1	4-40 UNC	Black Insulator	Reel Packaging (160 connectors) see page 2/2					HARTING EURL F-95972 Paris			TB 09 55 466 x816	Blatt/ Page 1 / 2	
09554666816.741	2													
09554667816.741	3													
Part number	PL	Thread	Index designation			Mod.	Dot.	Name					Sub.	





See TB 09 55 466 x816 folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2-A

				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-SUB Low Profile 37p Male Right angled SMT with die casted grounds and 4-40 UNC nuts	Maßstab/ Scale	
			Detail.	29Sep2010	ED				
			Insp.						
			Stand.						
			HARTING EURL F-95972 Paris					TB 09 55 466 x816	Blatt/ Page 2 / 2
36152	29Sep2010	ED							
Mod.	Dot.	Name							
							Sub.		