

Search within category

GO

BUY NOW

DESIGN / INSTALL



CJ6X88TGP

Category 6A, RJ45, 10 Gb/s, 8-position, 8-wire universal module.

- Specs
- Packaging Details
- Documents

★ Add to Favorites

Add to BOM

Module Type	Mini-Com
Material	ABS/Polycarbonate
Operating Temperature	-14°F to 149°F (-10°C to 65°C)
Storage Temperature	-40°F to 158°F (-40°C to 70°C)
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

We Welcome Your Feedback! Help Us Improve
By Taking Our Short Survey

Give Feedback