




Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description		Date	Approved	
Shape	Rectangle		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering		2/5/2014	J.S.	
Resonant Frequency	480	(Hz)							
Frequency Range	480 ~ 20,000	(Hz)							
SPL @ 10cm	87	(dBA)							
Impedance	8	(Ohm)							
Cone Material	Cloth								
Nominal Power	1.0	(W)							
Max Power	1.5	(W)							
Mount Type	Frame Mount								
Operating Temperature	-25 ~ +55	°C							
Storage Temperature	-25 ~ +55	°C	 DB UNLIMITED	Drawn by	Date	Checked by	Date	Approved by	Date
Weight	6	(g)		G.W.	1/27/2014	C.E.	1/29/2014	J.S.	2/5/2014
			Dynamic Speaker			SC400408-2			