

TMB-CP 2,5/10-C 500 - 3207868

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 058117
GTIN	4046356058117
Weight per Piece (excluding packing)	252.000 g
Custom tariff number	85444290
Country of origin	Poland

Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals

Approvals

Approvals


CSA / UL Recognized / cUL Recognized / cULus Recognized


Ex Approvals


Approval details

TMB-CP 2,5/10-C 500 - 3207868

Approvals

CSA		http://www.csagroup.org/services/testing-and-certification/certified-product-listing/	13631
		C	
mm ² /AWG/kcmil			14
Nominal current I _N			20 A
Nominal voltage U _N			600 V

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
mm ² /AWG/kcmil			14
Nominal current I _N			20 A
Nominal voltage U _N			600 V

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 118976
mm ² /AWG/kcmil			14
Nominal current I _N			15 A
Nominal voltage U _N			600 V

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	
------------------	---	---	--