Part Number : 192150037
Product Description : VibraKrimp Step Down Butt Splice from 8 to 12/10 AWG Wire, Carton
Series Number : 19215
Status : Active
Product Category : Splices
Engineering Part Number : DC-354



Documents and Resources

Drawings

192150037_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19215
Description	VibraKrimp Step Down Butt Splice from 8 to 12/10 AWG Wire, Carton
Comments	Step down: 8 to 12/10 AWG
Product Name	VersaKrimp
Style	Step Down
Type	Butt Splice
UPC	800755062571

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	4.705/g
Packaging Type	Carton
Temperature Range - Operating	149°C
Wire Insulation Diameter	N/A
Wire Size (AWG)	10, 2, 8

Downloaded from Arrow.com.

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	192860117
Die Set (Large) for the HHLS Hydraulic Crimper	192900001
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	640013900
RHT1080 Hand Crimp Tool	640034400
Square “DIN” style dies for 8 AWG	640037670
Crimp Head for the AT-200 Pneumatic Hand Tool	640074400

Downloaded from Arrow.com.