
APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/31/11	
A		UPDATE DRAWING	8/5/20	AY/LW
B		CORRECTED LENGTH FORMULA	3/30/21	SS



SPECIFICATIONS:
Material:
Insulator: PBT, glass fiber, rated UL 94V–0
Insulator color: Black
Contacts: Phosphor Bronze
Plating:
Gold over Nickel underplate on contact area,
Tin over Nickel underplate on solder tails.
Electrical:
Current rating: 1 Amp.
Contact resistance: 15 mohms Max.
Insulation resistance: 1,000 Mohms @ 500 VDC
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: –40°C to +105°C
Environmental:
Lead free, RoHS compliant

RoHS COMPLIANT

Positions: 06 thru 68
A = .079 [2.00] X No. of Spaces + .244 [6.20]
B = .079 [2.00] X No. of Spaces
C = .079 [2.00] X No. of Spaces + .039 [1.00]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	TW	8/31/11
CHECKED	AY	8/31/11
APPROVED		

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
2.0mm IDC TRANSITION PLUG, SEL GOLD PLATED

SIZE	PART NO.	REV.
X	2FTR-XX-SG	B

REF: S00087T | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.