

## YRV8CV10L, Uninsulated Reducing Splice For 8 AWG and 12 - 10 AWG

By Burndy

Catalog # [YRV8CV10L](#)



Cu Reducer Butt Splice, W/InspWindow, Barrel X:8 Barrel Y:10-12, 1.15" L, Tin Plated.

### Features

- Constructed from pure electrolytic copper tubing for optimal conductivity
- Tin plated to resist corrosion

### Application

For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)

### General

Catalog Number	YRV8CV10L
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Type	Reducing Splices
UPC	781810026380
UPC 14 Digit GTIN	00781810026380

### Dimensions

Dimension - A Outside	0.27 in
Diameter inch	
Dimension - B Length fraction	7/16 in
Dimension - B Outside	0.21 in
Diameter inch	
Dimension - Length BB inch	0.53 in

Length 1.15 in

### Conductor Related

Conductor - Copper Flex H Size	N/A
B Range	
Conductor - Copper Str Size B	10
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	1

### Product Assets

<a href="#">3D Models - YRV8CV10L_MODEL-STEP</a>
<a href="#">3D Models - YRV8CV10L_MODEL-PDF</a>
<a href="#">3D Models - YRV8CV10L_MODEL-IGES</a>
<a href="#">Catalogs - BURNDY Master Catalog - Section B - Small Terminals</a>
<a href="#">Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog</a>
<a href="#">Interactive Catalog - BURNDY Full-Line Digital Catalog</a>
<a href="#">Sales Drawings - 50094202</a>
<a href="#">Specifications - YRV8CV10L</a>



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-YRV8CV10L-SPEC-EN | REV 7/2025