

Representative Image

Catalog No. TC342A

Description: 2WAY ADH MTG BASE 1.1X1.1IN NAT NYL

UPC No 786210823133

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Two-Way Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Height of 6.4mm (0.25 Inches), Self-Adhesive Mounting Method, Bulk Pack

Descriptors

Category	Cable tie mounts
Special Features	One-piece molding - no lost parts

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Self-Adhesive
Operating Temperature	up to 149 F

Classifications

Brand Name	Ty-Rap

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	28.9 mm
Length	1.13 inch
Width	28.6 mm
Width	1.13 inch
Height	6.4 mm
Height	0.25 inch
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

by ABB

Downloaded from Arrow.com.

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.