







PCB layout

Specifications:


Current Rating:1.5A AC/DC
Voltage Rating:30V AC/DC
Contact Resistance:30m ohm. Max.
Insulation Resistance:1,000M ohm. min.
Withstanding Voltage:500V AC For One Minute
Operating Temperature Range:-40°C ~ +105°C

Material and Finish

Insulator:LCP (UL94V-0)
Insulator Color:Black
Contact:Brass
Plating:30u" Gold Plated on Contact Area
Tin Plated on Solder Tail.
Shell:Brass,Nickel Plated

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE:	CnC Tech Industrial Cable and Connector Technology		
					CHECKED:			.X=±0.20 X°.=±5° .XX=±0.10 .X°=±3°
				UNIT: MM		DESCRIPTION:	SIZE	
				APPROVAL:	SCALE:1:1	USB A TYPE SMD W/KINK TYPE, 30 u"		
					SHEET: 1 / 2	PART NO:	A4	
					PROJECTION: 			
REV	DATE	FILE	BY			1002-002-01100-TR		



Note:
1.Dimension:
Carton Size:350X350X296 (mm)
2.Qunntity:
200 Pcs/R
7 R/Carton
Q'TY: 1400pcs

Pin. NO	W	Pcs/R	R/Carton	Q'TY
04	32	200	7	1400

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 X°. =±5° .XX=±0.10 .X° =±3°	CnC Tech Industrial Cable and Connector Technology			
				CHECKED:	UNIT: MM	DESCRIPTION: USB A TYPE SMD W/KINK TYPE, 30 u"	SIZE		
					SCALE:1:1				
				APPROVAL:	SHEET: 2 / 2	PART NO: 1002-002-01100-TR	A4		
					PROJECTION: 				
REV	DATE	FILE	BY						