

Part Number : 5988330117F





Surface Mount LED Selector Guide

General Description

Lens Color	Water Clear
Series	598
Description	SM LED 1208 ALINGAP 7 REEL
Package Options	7" reel 3,000pcs / reel
Viewing Angle	160°

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	20mA
Reverse Voltage	5v
Operating Temperature	-40~+100 °C
Storage Temperature	-40~+100 °C

Operating Characteristics

Color	Orange 
Power Dissipation Max	48nW