

Conductor marker - UC-WMC 4,4 (30X5,5) VT



0825375

<https://www.phoenixcontact.com/us/products/0825375>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Conductor marker, Sheet, violet, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: clip on, cable diameter range: 2.8 ... 4.4 mm, lettering field size: 30 x 5.5 mm, Number of individual labels: 9

Your advantages

- The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial Data

Item number	0825375
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to Order (non-returnable)
Sales Key	B12
Product Key	BG2217
Catalog Page	Page 204 (C-3-2017)
GTIN	4046356350471
Weight per Piece (including packing)	9.34 g
Weight per Piece (excluding packing)	9.34 g
Customs tariff number	39269097
Country of origin	PL

Conductor marker - UC-WMC 4,4 (30X5,5) VT



0825375

<https://www.phoenixcontact.com/us/products/0825375>

Technical Data

Product properties

Product type	Conductor marking
Type	Card form

Marking

Number of individual labels	9
Number of individual labels per row	3

Marking technology

Device	5147999 BLUEMARK CLED
Printability	UV LED technology

Dimensions

Width	5.5 mm
Length	30 mm

External dimensions

Outside diameter	2.8 mm ... 4.4 mm
------------------	-------------------

Material specifications

RoHS compliant	yes
Color	violet
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

Cable / line

External cable diameter	2.8 mm ... 4.4 mm
-------------------------	-------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Conductor marker - UC-WMC 4,4 (30X5,5) VT



0825375

<https://www.phoenixcontact.com/us/products/0825375>

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	clip on
---------------	---------

Conductor marker - UC-WMC 4,4 (30X5,5) VT



0825375

<https://www.phoenixcontact.com/us/products/0825375>

Classifications

ECLASS

ECLASS-9.0	27400401
ECLASS-10.0.1	27400401
ECLASS-11.0	27281102

ETIM

ETIM 8.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Conductor marker - UC-WMC 4,4 (30X5,5) VT



0825375

<https://www.phoenixcontact.com/us/products/0825375>

Accessories

Magazine

Magazine - P1 UC-MAG 2 - 5146082

<https://www.phoenixcontact.com/us/products/5146082>

Magazine, for CMS-P1-PLOTTER, for accommodating UC-WMC 4.4...



Ink cartridge

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662

<https://www.phoenixcontact.com/us/products/5146662>

Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge



Conductor marker - UC-WMC 4,4 (30X5,5) VT



0825375

<https://www.phoenixcontact.com/us/products/0825375>

Ink cartridge

Ink cartridge - BLUEMARK FLUID-CARTRIDGE - 5147421

<https://www.phoenixcontact.com/us/products/5147421>

Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge



Ink cartridge

Ink cartridge - BM ID-CARTR. BK - 1044345

<https://www.phoenixcontact.com/us/products/1044345>

Replacement UV fluid, 23 ml, color: black



Conductor marker - UC-WMC 4,4 (30X5,5) VT

0825375

<https://www.phoenixcontact.com/us/products/0825375>



Ink cartridge

Ink cartridge - BM ID-CARTR. CY - 1044346

<https://www.phoenixcontact.com/us/products/1044346>

Replacement UV fluid, 23 ml, color: cyan



Ink cartridge

Ink cartridge - BM ID-CARTR. YE - 1044348

<https://www.phoenixcontact.com/us/products/1044348>

Replacement UV fluid, 23 ml, color: yellow



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com