

Product mass

Precautions for use

General notes

F-730

made in JAPAN



Horizontal installation type

DIN rail mounting

2020-01-09

[Notice of partial product changes.](#) PDF

[See other change notifications](#)

Order model number

Order model number F-730

Order example F-730

Basic information

Dimension

Optional

Conformity product / Mate product

Download

Detent (F-1000-S1) mounting example

When installing with 1P, it can be installed so that the main body does not rotate.

[Add to My List](#) >

[Sample request \(Only available in Japan\)](#) >


Mating fuse size

15mm×50mm

Basic information

Rating	600V-30A
Insulation resistance	DC500V, 100MΩ Min
Withstand voltage	AC2500V (1minute)
Main insulator	Phenolic (UL94V-0)
Terminal type	M4×8 Screw with washer
Terminal screw torque	1.2N·m
Body color	B (Black)
Installation screw torque	0.8N·m Max : with M4 screw
Installation	Screw or DIN Rail (Top hut type 35mm width)
Caution	Fuses with tin-plated caps are difficult to remove, so we recommend using ones other than tin-plated.

List of partial product change notifications

2020-01-09

[Notice of partial product changes.](#) PDF

2019-08-01

[Notice of partial product change notifications.](#) PDF

[Home](#)
[Product search](#)
[Product Category](#)
[About SATO PARTS](#)
[News classification](#)
[Contact us](#)
[Video channel](#)
[Download brochure](#)
[Environmental initiatives](#)
[Privacy policy](#)
[Cookie policy](#)
[Download terms](#)
[Terms of Use](#)