



## 4/0 Flex G,H,I,K,M, DLO, 4/0 AWG, Cu, 3/8" Stud, Std Barrel

By Burndy

Catalog # [YAG28LTC38FX](#)

4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, CU, 1 Hole, 3/8 Stud, Standard Barrel



### Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instruction

### Application

Wire Termination

### Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

### Conductor

Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Str Compact Size	"4/0 AWG"
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	4/0 AWG
Conductor - Copper Flex H Size	"4/0 AWG"

Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Str Navy Size	200
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	"4/0 AWG"

### Configuration

Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

### Current

Voltage Rating	35 kV
Voltage - Maximum	35000

### Dimensions

Dimension - Pad Width inch	1.14 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	62 mm
Dimension - Outside Diameter inch	0.77 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	1.03 in
Dimension - N inch	0.41 in

Dimension - Bolt Size inch 0.38  
Dimension - Length Overall inch 2.45 in

Plating Type Tin  
Finish Type Tin-Plated  
UPC 12 Digit 781810194355  
UPC 14 Digit GTIN 00781810194355

### General

Trade Name HYLUG™  
Die Index 15  
Feature - Barrel Type Standard  
Feature - Barrel Style Chamfered  
Plated Y  
Color Code Purple  
Sub Brand HYLUG  
UPC 781810194355  
Type Standard Barrel, Tin Plated  
Material Copper

### Logistics

Minimum Pack Quantity 1  
Pallet Quantity 17400  
Carton Quantity 50

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)  
[Installation Manual \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved  
BRDY-YAG28LTC38FX-SPEC-EN | REV 5/2026