



Part Number : [1300088080](#)

Product Description : Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (Straight) to Pigtail, 22-19 AWG, Black TPU Cable, 10.0m (32.81') Length

Series Number : 130008

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 303000B80M100



Documents and Resources

Drawings

[1300088080 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Relevant
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130008
Description	Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (Straight) to Pigtail, 22-19 AWG, Black TPU Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	889056891042

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	300V

Physical

Cable Diameter	10.20mm (.402")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPU

Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	1553.530/g
Orientation	Straight to Pigtail
Poles	19
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	19, 22

This document was generated on Dec 18, 2025